

300 Bar EXELTOP Packages for ARCAL™ Welding Gases



- 300 Bar 33L cylinder for easier handling and transportation
- Contains similar amount of gas as a standard 50L cylinder
- Reduces cylinder changeover downtime can be switched on and off in single action
- Includes innovative EXELTOP cylinder top with an easy to use built in regulator
- Available in Argon and Argon Mixtures from our ARCAL Welding Range
- Gas is compliant with BS EN ISO 14175:2008

EXELTOP

From the protective cap, through to the unique and patented On/Off lever, the EXELTOP valve is packed with features designed to make it safe and easy to use, whilst saving both time and money.

Key Features of EXELTOP

1. Protective casing gives complete protection of the integrated valve and regulator.
2. Built in regulator allows the user to adjust the pressure/flow using the handwheel.
3. The flowmeter allows the welder to set the flow rate to suit the welding process.
4. Integral gauge enables the user to view the content without the use of a regulator.
5. On/Off Lever. The cylinder can be opened and closed in a single action and provides a fast acting emergency cut off.
6. Quick connection saves time and allows rapid change over with no requirement for any spanners or other tools.



For further information on EXELTOP:

Call us on **0800 637737**

email us on **genenq.ALUK@airliquide.com**

visit our website **www.airliquide.co.uk**



Air Liquide UK Limited, Station Road, Coleshill, Birmingham B46 1JY.
Tel: 0800 637737 Email: genenq.ALUK@airliquide.com

www.airliquide.co.uk



The world leader in gases, technologies and services for Industry and Health, Air Liquide is present in 73 countries with approximately 67,100 employees and serves more than 3.9 million customers and patients.