

300 Bar SMARTOP™ Packages for ARCAL™ Welding Gases



- 300 Bar high capacity cylinders for maximum product availability
- More gas in every cylinder - minimises cylinder stocks
- Reduces cylinder handling and changeover downtime
- Increases productivity
- Includes innovative SMARTOP™ cylinder valve with multiple user benefits
- Available in Argon and Argon Mixtures from our Arcal Welding Range
- Gas is compliant with BS EN ISO 14175:2008

SMARTOP™

An innovative and ergonomically designed product for all welding applications.

Key Features of SMARTOP™

1. ON/OFF Lever. Cylinder can be opened and closed in a single action and provides a fast acting emergency cut off.
2. Ergonomic cap which protects valve from shocks and facilitates ease of handling.
3. Connect the regulator,* lift the lever and then ready for use.
4. Integral gauge enables the user to view the content without the use of a regulator.
5. Built-in flow restriction protects users from exposure to full cylinder pressure.
6. Open valve design, hence minimises the build up of unwanted substances.
7. Built-in Residual Pressure Valve (RPV) ensures cylinder integrity and prevents back flow contamination during use and storage.

*For safety reasons, all 300 Bar cylinders have a different valve connection to lower pressure cylinders. A 300 Bar rated regulator with NEVOC (ISO 5145) valve connection is required for use with the SMARTOP™ valve. Contact your Air Liquide representative for further information.



For further information on SMARTOP™:

Call us on **0800 637737**

email us on **genenq.ALUK@airliquide.com**

visit our website **www.airliquide.co.uk**



Air Liquide UK Limited, Station Road, Coleshill, Birmingham B46 1JY.
Tel: 0800 637737 Email: genenq.ALUK@airliquide.com

www.airliquide.co.uk



The world leader in gases, technologies and services for Industry and Health, Air Liquide is present in 73 countries with approximately 67,100 employees and serves more than 3.9 million customers and patients.